

**XEROX**

Technology | Document Management | Consulting Services

## Recommended Xerox Media for Xerox DocuColor 6060 (EUROPE)

**Revision:4.0 August 2007**

Last revision Feb 2007

This supersedes any previous Recommended Media for Xerox DocuColor 6060 list.

Any additions or part number changes since the last publication are indicated in Blue print.

**Important Note:**

Media recommendations made in this publication are based on qualification tests conducted using standard test images with moderate to heavy image area coverage.

Test machines are maintained within specifications defined by user documentation.

\* Testing environment Temperature 23 degreesC±2, Relative Humidity 50% ±5. Relative Humidity range 20-50%.

Reliability is based on your operating environment and application mix.

Machine reliability specifications may be affected by high usage of heavy weight and specialty stocks.

In addition, variances in machine reliability may occur due to extended use of some media types.

© 2005 Xerox Corporation. All rights reserved.

Xerox®, the stylized X®, and all Xerox product names and product names and product numbers mentioned in this publication are trademarks of Xerox Corporation.

Other company trademarks are also acknowledged.

**Warranty disclaimer:**

Xerox makes no guarantees or warranties, either expressed or implied, concerning the performance, use or replacement of non-Xerox branded media or throughput products.

Customers should inquire directly of their paper distributor or manufacturer for any guidance when purchasing a particular media product for the first time, customers are advised to purchase small quantities to insure that their expectations are met.

The quality of Xerox supplies is consistent from ream to ream and is backed by a 100% guarantee.

The quality of non-Xerox branded paper may vary from ream to ream or carton to carton, so for optimum performance on Xerox Colour equipment, use only the best - Xerox supplies.

**EUROPEAN RECOMMENDED MATERIALS LIST- DOCUCOLOR 6060**

Weight Range Specification Instructions for Printing one side (Simplex) or two sides (Duplex)	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight of the paper in grams per square meter	DocuColor 6060 Trays/ Weight Selection and Best Practices for Operation										
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4
Weight Range Specification						64-74 gsm		75-105 gsm		106-135 gsm		136-150 gsm		151-220 gsm		221-300 gsm	
Instructions for Printing one side (Simplex) or two sides (Duplex)						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex
<b>Business Papers (Bond, xerographic, and laser grades)</b>																	
<b>Xerox Digital Colour Impressions 80 gsm</b>	A	3R97661	3R97662		3R97991	80			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Colotech + Gold 90 gsm</b>	A		3R97990			90			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Colotech + 90 gsm</b>	A	3R97988			3R95838	90			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Impressions 90 gsm</b>	A		3R94642		3R94643	90			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Colotech + Gold 100 gsm</b>	A	3R94641			3R97665	90			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Colotech + 100 gsm</b>	A	3R97663	3R97664		3R97956	90			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Colotech + 100 gsm</b>	A		3R97955			100			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Colotech Natural White 100 gsm</b>	A	3R97993			3R95839	100			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Colotech + 100 gsm</b>	A		3R94647		3R94648	100			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Colotech Natural White 100 gsm</b>	A	3R94646			3R97397	100			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Impressions 100 gsm</b>	A	3R97102	3R97103			100			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Impressions 100 gsm</b>	A		3R97667		3R97668	100			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Colotech+ Gold 120 gsm</b>	B	3R97666	3R97959		3R97960	120			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Colotech+ 120 gsm</b>	B		3R97958			120			OK All Trays	OK All Trays							
<b>Xerox Digital Colour Impressions 120 gsm</b>	A	3R94651			3R95840	120			OK All Trays	OK All Trays							
<b>Uncoated Heavy Stocks</b>																	
<b>Xerox Digital Colour Impressions 160 gsm</b>	A		3R98008		3R98686	160								Tray 3 & 4	Tray 3 & 4		
<b>Xerox Digital Colour Colotech + Gold 160 gsm</b>	A	3R98007			3R97965	160			OK All Trays	OK All Trays				OK All Trays	OK All Trays		
<b>Xerox Digital Colour Colotech + 160 gsm</b>	A		3R97964			160			OK All Trays	OK All Trays				OK All Trays	OK All Trays		
<b>Xerox Digital Colour Colotech Natural White 160 gsm</b>	A		3R94652		3R95841	160			OK All Trays	OK All Trays				OK All Trays	OK All Trays		
<b>Xerox Digital Colour Colotech + 160 gsm</b>	A	3R94656			3R94658	160			OK All Trays	OK All Trays				OK All Trays	OK All Trays		
<b>Xerox Digital Colour Colotech + 160 gsm</b>	A		3R95957		3R97276	160			OK All Trays	OK All Trays				OK All Trays	OK All Trays		
<b>Xerox Digital Colour Colotech + Gold 200 gsm</b>	A	3R95956			3R97969	200			OK All Trays	OK All Trays				OK All Trays	OK All Trays		
<b>Xerox Digital Colour Colotech + Gold 200 gsm</b>	A		3R97968			200			OK All Trays	OK All Trays				OK All Trays	OK All Trays		
<b>Xerox Digital Colour Colotech + Gold 200 gsm</b>	A	3R97967				200			OK All Trays	OK All Trays				OK All Trays	OK All Trays		



**EUROPEAN RECOMMENDED MATERIALS LIST- DOCUCOLOR 6060**

Weight Range Specification Instructions for Printing one side (Simplex) or two sides (Duplex)	A	Standard Cut Sizes				Grammage Weight of the paper in grams per square meter	DocuColor 6060 Trays/ Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			
		64-74 gsm		75-105 gsm			106-135 gsm		136-150 gsm		151-220 gsm		221-300 gsm					
Simplex		Duplex		Simplex		Duplex		Simplex		Duplex		Simplex		Duplex				
Xerox Digital Colour Colotech + 200 gsm	A		3R94662		3R95842	200								OK All Trays	OK All Trays			
		3R94661				200									OK All Trays	OK All Trays		
Xerox Digital Colour Colotech Natural White 200 gsm	A				3R97277	200								OK All Trays	OK All Trays			
		3R95958	3R95959			200									OK All Trays	OK All Trays		
Xerox Digital Colour Colotech + Gold 220 gsm	A		3R97972			220								OK All Trays	OK All Trays			
		3R97971			3R97973	220									OK All Trays	OK All Trays		
Xerox Digital Colour Colotech + 220 gsm	A		3R94669			220								OK All Trays	OK All Trays			
		3R94668		3R94670		220									OK All Trays	OK All Trays		
Xerox Digital Colour Colotech + Gold 250 gsm	A		3R97976			250										OK All Trays	Manual Duplex	
		3R97975			3R97977	250										OK All Trays	Manual Duplex	
Xerox Digital Colour Colotech + 250 gsm	A				3R95844	250								OK All Trays	Manual Duplex			
		3R94671	3R94672	3R94673		250									OK All Trays	Manual Duplex		
Xerox Digital Colour Impressions 250 gsm	A		3R97671			250								OK All Trays	Manual Duplex			
		3R96687			3R97672	250									OK All Trays	Manual Duplex		
Xerox Digital Colour Colotech + Gold 280 gsm	A		3R97980			280								OK All Trays	Manual Duplex			
		3R97979			3R97981	280									OK All Trays	Manual Duplex		
Xerox Digital Colour Colotech + 280 gsm	A		3R97097	3R97098		280								OK All Trays	Manual Duplex			
					3R97985	280									OK All Trays	Manual Duplex		
Xerox Digital Colour Colotech + Gold 300 gsm	A		3R97983	3R97984		300								OK All Trays	Manual Duplex			
					3R97554	300									OK All Trays	Manual Duplex		
Xerox Digital Colour Colotech + 300 gsm	A		3R97552	3R97553		300								OK All Trays	Manual Duplex			
						300									OK All Trays	Manual Duplex		
<b>Coated Text or Book Stocks C2S</b>	Decurler Setting paper type																	
Xerox Digital Colour Colotech + Silk Coated 120 gsm	A		3R97593		3R97594	120					OK All Trays	OK All Trays						
		3R97592				120					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + Gloss Coated 120 gsm	A				3R97576	120					OK All Trays	OK All Trays						
		3R97574	3R97575			120					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + Silk Coated 140 gsm	A		3R97595	3R97596		140							OK All Trays	OK All Trays				
					3R97597	140								OK All Trays	OK All Trays			
Xerox Digital Colour Colotech + Gloss Coated 140 gsm	A		3R97578			140								OK All Trays	OK All Trays			
		3R97577			3R97579	140									OK All Trays	OK All Trays		

### EUROPEAN RECOMMENDED MATERIALS LIST- DOCUCOLOR 6060

	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight of the paper in grams per square meter	DocuColor 6060Trays/ Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4	
Weight Range Specification Instructions for Printing one side (Simplex) or two sides (Duplex)						64-80 gsm		81-105 gsm		106-135 gsm		136-150 gsm		151-220 gsm		221-300 gsm		
						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
<b>Coated Heavy Stocks</b>																		
<b>C2S</b>																		
Xerox Digital Colour Colotech + Silk Coated 170 gsm	A	3R97598	3R97599		3R97600	170										OK All Trays	OK All Trays	
Xerox Digital Colour Colotech + Gloss Coated 170 gsm	A	3R97580	3R97581		3R97582	170										OK All Trays	OK All Trays	
Xerox Digital Colour Colotech + Silk Coated 210 gsm	A		3R97602		3R97603	210										OK All Trays	OK All Trays	
Xerox Digital Colour Colotech + Gloss Coated 210 gsm	A	3R97601			3R97585	210										OK All Trays	OK All Trays	
Xerox Digital Colour Colotech + Silk Coated 250 gsm	A		3R97605		3R97606	250										OK All Trays	Manual Duplex	
Xerox Digital Colour Colotech + Gloss Coated 250 gsm	A	3R97604	3R97587		3R97588	250										OK All Trays	Manual Duplex	
Xerox Digital Colour Colotech + Silk Coated 280 gsm	A	3R97586			3R97609	280										OK All Trays	Manual Duplex	
Xerox Digital Colour Colotech + Gloss Coated 280 gsm	A	3R97607	3R97608		3R97591	280										OK All Trays	Manual Duplex	
		3R97589	3R97590			280										OK All Trays	Manual Duplex	
<b>Super Gloss Coated Heavy Stocks</b>																		
<b>C1S</b>																		
Xerox Digital Colour Colotech + SuperGloss 135 Image quality will not be as good on second side	A	3R97679				135							OK All Trays	OK All Trays				
Xerox Digital Colour Colotech + SuperGloss 160 Image quality will not be as good on second side	A	3R97680	3R97681			160										OK All Trays	OK All Trays	
Xerox Digital Colour Colotech + SuperGloss 210 Image quality will not be as good on second side	A	3R97682	3R97683		3R97684	210										OK All Trays	OK All Trays	
Xerox Digital Colour Colotech + SuperGloss 250 Image quality will not be as good on second side	A	3R97686	3R97687		3R97688	250										OK All Trays	Manual Duplex	
						250										OK All Trays	Manual Duplex	
<b>Specialties</b>																		
Xerox Digital Colour Colotech Super 210 A4 Prescored White	A	3R97685	Second side image quality will not be as good as side one			210										OK All Trays	OK All Trays	
Xerox DocuCard 500 sheet box	A	3R97571	Maximum of 50 sheet stacks			160										OK All Trays	OK All Trays	
Xerox DocuGlossCard 500 sheet box	A	3R97678	Maximum of 50 sheet stacks			120										OK All Trays	OK All Trays	
Xerox ValuPeelCard Coated 500 sheet box	A	3R97953	Maximum of 50 sheet stacks			216										OK All Trays	OK All Trays	
Xerox ValuPeelCard Uncoated 500 sheet box	A	3R97952	Maximum of 50 sheet stacks			216										OK All Trays	OK All Trays	
Xerox ValuPerfCard Coated 500 sheet box	A	3R97677	Maximum of 50 sheet stacks			216										OK All Trays	OK All Trays	
Xerox ValuPerfCard Uncoated 500 sheet box	A	3R97690	Maximum of 50 sheet stacks			216										OK All Trays	OK All Trays	
Xerox Premium Never Tear 95 microns	Default	3R98056	Select Uncoated 151-220 gsm mode in Tray 3. Each batch run should not be more than 500 simplex. Must run 50 sheets paper between batches. Static may cause issues in stacking			95 microns										all Trays Simplex only	Manual Duplex	
Xerox Premium Never Tear 120 microns	Default	3R98058	Select Uncoated 151-220 gsm mode in Tray 3. Each batch run should not be more than 500 Simplex. Must run 50 sheets paper between batches. Static may cause issues in stacking			120 microns										all Trays Simplex only	Manual Duplex	
Xerox DuraPaper X250	A				3R97513	250 microns										OK All Trays	Manual Duplex	

**EUROPEAN RECOMMENDED MATERIALS LIST- DOCUCOLOR 6060**

	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m2) Weight of the paper in grams per square meter	DocuColor 6060Trays/ Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			
		Weight Range Specification					64-80 gsm		81-105 gsm		106-135 gsm		136-150 gsm		151-220 gsm		221-300 gsm	
Instructions for Printing one side (Simplex) or two sides (Duplex)						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex			
<b>Specialties</b>		Various																
Xerox DocuPac Glossy White Presentation folder	A	Select Coated 151-220 gsm mode - load glossy side up, score line trailing 3R97251				210								OK All Trays	OK All Trays			
Xerox DocuPac Matt Presentation folder	A	Select uncoated 151-220 gsm mode- load glossy side up, score line trailing. 3R97353 [image quality not as good as Colotech +]				180								OK All Trays	OK All Trays			
Xerox Laser Business Cards 10-UP	A	Select uncoated 151-220 gsm mode in Tray image side up. 3R97512				195										OK All Trays	Manual Duplex	
Xerox Colotech Supergloss Document Folder	A	Select coated 221-280 gsm mode for glossy side, uncoated 221-300 gsm for matt side 3R97634				250										OK All Trays	Manual Duplex	
Xerox Laser Window Graphics Clear (window decal)	A	Select coated 151-220 gsm mode - image side up. 3R97494				125 micron								OK All Trays	OK All Trays			
Xerox Laser Window Graphics Opaque White (window decal)	A	Select coated 151-220 gsm mode - image side up. 3R97511				125 micron								OK All Trays	OK All Trays			
		3R97539																
Xerox Transfer Paper	A	Select coated 151-220 gsm mode - image side up. Each batch run should not exceed 500 sheets. 100 sheets Colotech Paper should be run between batches. No more than 500 sheets per day. 3R97949												OK All Trays				
		3R97951																
<b>Tab Stock</b>	Decurler Setting paper type																	
Xerox Digital Colour Colotech Tabs White 100 X 5 reverse	B	Select Uncoated 151-220 gsm mode. Load SEF 3R97231				200								Tray 3 Only	Tray 3 Only			
Xerox Mylar Tabs White 100 X 5 reverse	B	3R97232												Tray 3 Only	Tray 3 Only			
Xerox Mylar Tabs White 50 X 10 reverse	B	3R97229												Tray 3 Only	Tray 3 Only			
Xerox Mylar Tabs White 50 X 10 reverse	B	3R97230												Tray 3 Only	Tray 3 Only			
<b>Transparencies</b>	Decurler Setting paper type																	
Xerox Universal Transparency with Paper Backing <sup>250 SHEET</sup>	Default	FOR HIGH PRINT QUALITY Select Uncoated 221-300 gsm mode. Load transparency facing up. 3R98199				100 micron										OK All Trays		
Xerox Universal Transparency with Paper Backing SRA3	Default	3R98201				100 micron										OK All Trays		
Xerox Universal Transparency with Paper Backing <sup>250 SHEET</sup>	Default	FOR HIGH SPEED (STANDARD PRINT QUALITY) Select Uncoated 151-220 gsm mode. Load transparency facing up. 3R98199				100 micron								OK All Trays				
Xerox Universal Transparency with Paper Backing SRA3	Default	3R98201												OK All Trays				
<b>Label Stock</b>	Decurler Setting paper type																	
Xerox Colour Laser Printer Labels																		
1 PER A4	C	3R93872				190								OK All Trays				
6 PER A4	C	3R93873				190								OK All Trays				
8 PER A4	C	3R93874				190								OK All Trays				
14 PER A4	C	3R93875				190								OK All Trays				
24 PER A4	C	3R97524				190								OK All Trays				
Xerox laser Colour Gloss Coated Labels																		
1 PER A4	C	3R97288				190								OK All Trays				
2 to view CD labels	C	3R97287				190								OK All Trays				
Xerox Colotech + Matt Face																		
Xerox CD label + CD insert Comb Box	C&A	3R97515				190 & 120								OK All Trays				
Xerox Durapaper Label (polyolefin face material) 1 PER A4	C	3R97344				250								OK All Trays				
Xerox Glossy White Self Adhesive Label A4																		
	Default	3R97245				190								OK All Trays				
Xerox Glossy White Self Adhesive Label SRA3																		
	Default	3R97348				190								OK All Trays				
Xerox Crystal Clear Adhesive Label A4																		
	Default	3R97244				190								OK All Trays				
Xerox Crystal Clear Adhesive Label SRA3																		
	Default	3R97347				190								OK All Trays				



**EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 6060**

	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m <sup>2</sup> ) <small>Weight of the paper in grams per square meter</small>	DocuColor 6060Trays/ Weight Selection and Best Practices for Operation										
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		
Weight Range Specification						64-74 gsm		81-105 gsm		106-135 gsm		136-150 gsm		151-220 gsm		221- 300 gsm	
Instructions for Printing one side (Simplex) or two sides (Duplex)						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex
<b>Carbonless Paper</b>																	
Xerox Premium Digital Carbonless Paper						IOT Common Software V 2.191 must be installed, and fan disabled, prior to use*											
CB Singles White		3R99069				82			Tray 3 Only								
CB Singles White (PLE)		3R99088				82			Tray 3 Only								
CB Singles White (PSE)		3R99089				82			Tray 3 Only								
CB Singles Yellow		3R99080				82			Tray 3 Only								
CB Singles Pink		3R99083				82			Tray 3 Only								
CB Singles Blue		3R99082				82			Tray 3 Only								
CB Singles Green		3R99081				82			Tray 3 Only								
CFB Singles White		3R99070				86			Tray 3 Only								
CFB Singles Yellow		3R99071				86			Tray 3 Only								
CFB Singles Yellow (PLE)		3R99091				86			Tray 3 Only								
CFB Singles Yellow (PSE)		3R99092				86			Tray 3 Only								
CFB Singles Pink		3R99074				86			Tray 3 Only								
CFB Singles Pink (PLE)		3R99093				86			Tray 3 Only								
CFB Singles Blue		3R99072				86			Tray 3 Only								
CFB Singles Green		3R99073				86			Tray 3 Only								
CF Singles White	A	3R99075				82			Tray 3 Only								
CF Singles White (PLE)		3R99090				82			Tray 3 Only								
CF Singles Yellow		3R99076				82			Tray 3 Only								
CF Singles Pink		3R99077				82			Tray 3 Only								
CF Singles Pink (PLE)		3R99094				82			Tray 3 Only								
CF Singles Blue		3R99078				82			Tray 3 Only								
CF Singles Green		3R99079				82			Tray 3 Only								
A4+ CF Singles Yellow		3R99639				82			Tray 3 Only								
A4+ CF Singles Pink		3R99638				82			Tray 3 Only								
A4+ CF Singles Blue		3R99644				82			Tray 3 Only								
CF Singles Tag Cream		3R99146				170			Tray 3 Only					Tray 3 Only			
CF Singles Tag White		3R99147				170								Tray 3 Only			
A4+ CF Singles Tag Cream		3R99640				170								Tray 3 Only			
A4+ CF Singles Tag Pink		3R99641				170								Tray 3 Only			
2-Part White / Yellow		3R99105				82/82			Tray 3 Only								
2-Part White (PLE) / Yellow		3R99084	3R99133			82/82			Tray 3 Only								
2-Part White (PSE) / Yellow		3R99085				82/82			Tray 3 Only								
2-Part White / Pink		3R99107				82/82			Tray 3 Only								
3-Part Straight White / Yellow / Pink		3R99108	3R99134			82/82			Tray 3 Only								
3-Part Straight White (PLE) / Yellow (PLE) / Pink		3R99086				82/86/82			Tray 3 Only								
3-Part Straight White (PSE) / Yellow (PSE) / Pink		3R99087				82/86/82			Tray 3 Only								
3-Part Reverse Pink / Yellow / White		3R99109				82/86/82			Tray 3 Only								
4-Part Straight White / Yellow / Pink / Blue		3R99111				82/86/86/82			Tray 3 Only								
4-Part Reverse Blue / Pink / Yellow / White	A	3R99112				82/86/86/82			Tray 3 Only								
<b>* Contact your local Service Representative and refer to System Administration Guide for details</b>																	
<b>Xerox Colobind Gloss Covers</b>																	
Decurler Setting paper type						Limit Tray capacity to 50 sheets. Image quality can vary from good to fair depending on score quality. Slightly degraded image quality on uncoated side. Do not image within 6mm around the score lines. Manual duplex printing only.											
Post Script custom size required for 6mm, 9mm and 12 mm spines																	
Spine width 1.5 mm		3R98022				210										OK All Trays	Manual Duplex
Spine width 3 mm		3R98023				210										OK All Trays	Manual Duplex
Spine width 6 mm		3R98024				210										OK All Trays	Manual Duplex
Spine width 9 mm		3R98025				210										OK All Trays	Manual Duplex
Spine width 12 mm		3R98026				210										OK All Trays	Manual Duplex