



Recommended Xerox Media for Xerox® DocuColor® 5000AP

Version 2.0. August 2012

This supersedes any previous Recommended Media for Xerox DocuColor 5000AP

Important Notes:

Media recommendations made in this publication are based on qualification tests conducted using standard test images with moderate to heavy image area coverage. Test machines are maintained within specifications defined by user documentation.

* Testing environment: Temperature 23°C±2, Relative Humidity range 20-50 %.

Reliability is based on your operating environment and application mix.

Machine reliability specifications may be affected by high usage of heavy weight and specialty stocks. In addition, variances in machine reliability may occur due to extended use of some media types.

Warranty disclaimer:

Xerox makes no guarantees or warranties, either expressed or implied, concerning the performance, use or replacement of non-Xerox branded media or throughput products. Customers should inquire directly of their paper distributor or manufacturer for any guidance when purchasing a particular media product for the first time, customers are advised to purchase small quantities to ensure that their expectations are met. The quality of Xerox supplies is consistent from ream to ream and is backed by a 100% guarantee. The quality of non-Xerox branded paper may vary from ream to ream or carton to carton, so for optimum performance on Xerox Colour equipment, use only the best - Xerox supplies.

©2006-2012 Xerox Corporation. All rights reserved.

XEROX®, XEROX and Design® and DocuColor® are trademarks of or licensed to Xerox Corporation in the United States and/or other countries.

For the latest line of Xerox supplies contact your local Xerox representative or a recommended distributor. For the most recent version of this list visit www.xerox.com/europaper

European Recommended Materials List - DocuColor 5000AP

		Standard Cut Sizes			Grammage	DC5000AP Trays/Weight Selection and Best Practices for Operation											
		A4	A3	SRA3	Weight of the paper in grams per square meter	IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			
		210x297 mm	297x420 mm	320x450 mm		60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-300 gsm			
Weight Range Specification ----->					Simplex		Duplex		Simplex		Duplex		Simplex		Duplex		
Instructions for Printing one side (Simplex) or two sides (Duplex) ----->																	
Business Papers (Bond, xerographic, and laser grades)	Decurler Setting paper type																
Xerox Colour Impressions 80 gsm	A	003R97661	003R97662		80	OK All Trays	OK All Trays										
				003R98840	80	OK All Trays	OK All Trays										
Xerox Colotech+ Gold 90 gsm	A		003R98839		90			OK All Trays	OK All Trays								
		003R98837			90			OK All Trays	OK All Trays								
Xerox Colotech+ 90 gsm	A		003R94642	003R95838	90			OK All Trays	OK All Trays								
		003R94641			90			OK All Trays	OK All Trays								
Xerox Colour Impressions 90 gsm	A		003R97664	003R97665	90			OK All Trays	OK All Trays								
		003R97663			90			OK All Trays	OK All Trays								
Xerox Colotech+ Gold 100 gsm	A		003R98844	003R98845	100			OK All Trays	OK All Trays								
		003R98842			100			OK All Trays	OK All Trays								
Xerox Colotech+ 100 gsm	A		003R94647	003R95839	100			OK All Trays	OK All Trays								
		003R94646			100			OK All Trays	OK All Trays								
Xerox Colotech Natural White 100 gsm	A		003R97103		100			OK All Trays	OK All Trays								
		003R97102			100			OK All Trays	OK All Trays								
Xerox Colour Impressions 100 gsm	A		003R97667	003R97668	100			OK All Trays	OK All Trays								
		003R97666			100			OK All Trays	OK All Trays								
Xerox Colotech+ Gold 120 gsm	B		003R98848	003R98849	120					OK All Trays	OK All Trays						
		003R98847			120					OK All Trays	OK All Trays						
Xerox Colotech+ 120 gsm	B		003R94652	003R95840	120					OK All Trays	OK All Trays						
		003R94651			120					OK All Trays	OK All Trays						
Xerox Colour Impressions 120 gsm	A		003R97670		120					OK All Trays	OK All Trays						
		003R98685		003R97669	120					OK All Trays	OK All Trays						
Uncoated Heavy Stocks	Decurler Setting paper type																
				003R98686	160							OK All Trays	OK All Trays				
Xerox Colour Impressions 160 gsm	A		003R98008		160							OK All Trays	OK All Trays				
		003R98007			160							OK All Trays	OK All Trays				
Xerox Colotech+ Gold 160 gsm	A		003R98854	003R98855	160							OK All Trays	OK All Trays				
		003R98852			160							OK All Trays	OK All Trays				
Xerox Colotech+ 160 gsm	A		003R94657	003R95841	160							OK All Trays	OK All Trays				
		003R94656			160							OK All Trays	OK All Trays				
Xerox Colotech Natural White 160 gsm			003R95957		160							OK All Trays	OK All Trays				
		003R95956			160							OK All Trays	OK All Trays				
Xerox Colotech+ Gold 200 gsm	A		003R97968	003R97969	200										OK All Trays	OK All Trays	
		003R97967			200										OK All Trays	OK All Trays	
Xerox Colotech+ 200 gsm	A		003R94662	003R95842	200										OK All Trays	OK All Trays	
		003R94661			200										OK All Trays	OK All Trays	
Xerox Colotech Natural White 200 gsm	A		003R95959		200										OK All Trays	OK All Trays	
		003R95958			200										OK All Trays	OK All Trays	
Xerox Colotech+ Gold 220 gsm	A		003R97972	003R97973	220										OK All Trays	OK All Trays	
		003R97971			220										OK All Trays	OK All Trays	
Xerox Colotech+ 220 gsm	A			003R95843	220										OK All Trays	OK All Trays	
		003R94668		003R94669	220										OK All Trays	OK All Trays	

European Recommended Materials List - DocuColor 5000AP

		Standard Cut Sizes			Grammage	DC5000AP Trays/Weight Selection and Best Practices for Operation										
		A4	A3	SRA3	Weight (g/m ²)	IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		
		210x297 mm	297x420 mm	320x450 mm	Weight of the paper in grams per square meter	60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-300 gsm		
Weight Range Specification Instructions for Printing one side (Simplex) or two sides (Duplex) ----->					Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex		
Uncoated Heavy Stocks	Decurler Setting paper type															
Xerox Colotech+ Gold 250 gsm	A		003R98976	003R98977	250										OK All Trays	OK All Trays
		003R98975		003R95844	250										OK All Trays	OK All Trays
Xerox Colotech+ 250 gsm	A		003R94672		250										OK All Trays	OK All Trays
		003R94671			250										OK All Trays	OK All Trays
Xerox Colour Impressions 250 gsm	A		003R97671	003R97672	250										OK All Trays	OK All Trays
		003R98687		003R97981	250										OK All Trays	OK All Trays
Xerox Colotech+ Gold 280 gsm	A		003R98980		280										OK All Trays	OK All Trays
		003R98979		003R97099	280										OK All Trays	OK All Trays
Xerox Colotech+ 280 gsm	A		003R97098		280										OK All Trays	OK All Trays
		003R97097			280										OK All Trays	OK All Trays
Xerox Colotech+ Gold 300 gsm	A		003R97984		300										OK All Trays	OK All Trays
		003R97983		003R97554	300										OK All Trays	OK All Trays
Xerox Colotech+ 300 gsm	A		003R97553		300										OK All Trays	OK All Trays
		003R97552			300										OK All Trays	OK All Trays
Coated Text or Book Stocks	Decurler Setting paper type															
C25																
Xerox Colotech+ Silk Coated 120 gsm	A		003R90356	003R90357	120					OK All Trays	OK All Trays					
		003R90355		003R90338	120					OK All Trays	OK All Trays					
Xerox Colotech+ Gloss Coated 120 gsm	A		003R90337		120					OK All Trays	OK All Trays					
		003R90336		003R90360	120					OK All Trays	OK All Trays					
Xerox Colotech+ Silk Coated 140 gsm	A		003R90359		140							OK All Trays	OK All Trays			
		003R90358		003R90341	140							OK All Trays	OK All Trays			
Xerox Colotech+ Gloss Coated 140 gsm	A		003R90340		140							OK All Trays	OK All Trays			
		003R90339			140							OK All Trays	OK All Trays			
Coated Heavy Stocks	Decurler Setting paper type															
C25																
Xerox Colotech+ Silk Coated 170 gsm	A		003R90362	003R90363	170							OK All Trays	OK All Trays			
		003R90361		003R90344	170							OK All Trays	OK All Trays			
Xerox Colotech+ Gloss Coated 170 gsm	A		003R90343		170							OK All Trays	OK All Trays			
		003R90342		003R90366	170							OK All Trays	OK All Trays			
Xerox Colotech+ Silk Coated 210 gsm	A		003R90365		210									OK All Trays	OK All Trays	
		003R90364		003R90347	210									OK All Trays	OK All Trays	
Xerox Colotech+ Gloss Coated 210 gsm	A		003R90346		210									OK All Trays	OK All Trays	
		003R90345		003R90369	210									OK All Trays	OK All Trays	
Xerox Colotech+ Silk Coated 250 gsm	A		003R90368		250									OK All Trays	OK All Trays	
		003R90367		003R90350	250									OK All Trays	OK All Trays	
Xerox Colotech+ Gloss Coated 250 gsm	A		003R90349		250									OK All Trays	OK All Trays	
		003R90348		003R90372	250									OK All Trays	OK All Trays	
Xerox Colotech+ Silk Coated 280 gsm	A		003R90371		280									OK All Trays	OK All Trays	
		003R90370		003R90353	280									OK All Trays	OK All Trays	
Xerox Colotech+ Gloss Coated 280 gsm	A		003R90352		280									OK All Trays	OK All Trays	
		003R90351			280									OK All Trays	OK All Trays	

European Recommended Materials List - DocuColor 5000AP

		Standard Cut Sizes			Grammage	DC5000AP Trays/Weight Selection and Best Practices for Operation									
		A4 210x297 mm	A3 297x420 mm	SRA3 320x450 mm	Weight of the paper in grams per square meter	IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4	
Weight Range Specification ----->					60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-300 gsm		
Instructions for Printing one side (Simplex) or two sides (Duplex) ----->					Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
Super Gloss Coated Heavy Stocks C15	Decurler Setting paper type														
Xerox Colotech+ Supergloss 135 gsm Image quality will not be as good on second side	A	Select 106-135 gsm mode. Load with coated side up. 003R97679			135							OK All Trays	OK All Trays		
Xerox Colotech+ Supergloss 160 gsm Image quality will not be as good on second side	A	Select 187-220 gsm mode. Load with coated side up. 003R97680			160								OK All Trays		
			003R97681		160								OK All Trays		
Xerox Colotech+ Supergloss 210 gsm Image quality will not be as good on second side	A			003R97684	210								OK All Trays		
			003R97683		210								OK All Trays		
		003R97682			210								OK All Trays		
Xerox Colotech+ Supergloss 250 gsm Image quality will not be as good on second side	A	Select 221-300 gsm mode. Load with coated side up. 003R97686			250								OK All Trays		
			003R97687	003R97688	250								OK All Trays		
					250								OK All Trays		
Specialties	Decurler Setting paper type				Various										
Xerox Colotech Supergloss 210 A4 Prescored White	A	Second side image quality will not be as good as side one. 003R97685			210								OK All Trays		
Xerox ValuPerfCard Uncoated 500 sheet box	A	Maximum of 50 sheet stacks 003R97690			216								OK All Trays		
Xerox DuraPaper	A	Select Uncoated 187-220 gsm mode. Load image side up. 003R97513			250 microns								OK All Trays		
Xerox Laser Business Cards 10-up	A	Select Uncoated 187-220 gsm mode - image side up. 003R97512			195								OK All Trays		
Xerox Colotech Supergloss Document Folder	A	Select Coated 221-300 gsm mode for glossy side, Uncoated 221-280 gsm for matt side. 003R97634			250								OK All Trays		
Tab Stock	Decurler Setting paper type														
Xerox Colotech Tabs White 100x5 Reverse Collated	B	Feed long edge first, tabs trailing. 003R97231			200								OK All Trays		
Xerox Colotech Tabs White 50x10 Reverse Collated	B	003R97232			200								OK All Trays		
Xerox Reinforced Tabs White 100x5 Reverse Collated	B	003R97229			200								OK All Trays		
Xerox Reinforced Tabs White 100x10 Reverse Collated	B	003R97230			200								OK All Trays		

* Feed Long Edge First, Tabs Trailing

