



Recommended Xerox Media for Xerox® DocuColor® 8000AP/8000/7000AP/7000

Version 8.1. August 2012

This supersedes any previous Recommended Media for Xerox DocuColor 8000AP/8000/7000AP/7000

Important Notes:

Media recommendations made in this publication are based on qualification tests conducted using standard test images with moderate to heavy image area coverage. Test machines are maintained within specifications defined by user documentation.

* Testing environment: Temperature 23°C±2, Relative Humidity range 20-50 %.

Reliability is based on your operating environment and application mix.

Machine reliability specifications may be affected by high usage of heavy weight and specialty stocks. In addition, variances in machine reliability may occur due to extended use of some media types.

Warranty disclaimer:

Xerox makes no guarantees or warranties, either expressed or implied, concerning the performance, use or replacement of non-Xerox branded media or throughput products. Customers should inquire directly of their paper distributor or manufacturer for any guidance when purchasing a particular media product for the first time, customers are advised to purchase small quantities to ensure that their expectations are met. The quality of Xerox supplies is consistent from ream to ream and is backed by a 100 % guarantee. The quality of non-Xerox branded paper may vary from ream to ream or carton to carton, so for optimum performance on Xerox Colour equipment, use only the best - Xerox supplies.

©2003-2012 Xerox Corporation. All rights reserved.

XEROX®, XEROX and Design® and DocuColor® are trademarks of or licensed to Xerox Corporation in the United States and/or other countries.

For the latest line of Xerox supplies contact your local Xerox representative or a recommended distributor. For the most recent version of this list visit www.xerox.com/europaper

European Recommended Materials List - DocuColor 8000AP/8000/7000AP/7000

Weight Range Specification Instructions for printing one side (Simplex) or two sides (Duplex) ----->	Decurler Setting Paper Type	Standard Cut Sizes			Grammage Weight (g/m ²) Weight of the paper in grams per square metre	DC8000AP/8000/7000AP/7000 Trays/Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4	
		60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm					
		Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex		
Business Papers (bond, xerographic and laser grades)																	
Xerox Colour Impressions 80 gsm	A	003R97661	003R97662		80	OK All Trays	OK All Trays										
			003R98840		80	OK All Trays	OK All Trays										
					90			OK All Trays	OK All Trays								
Xerox Colotech+ Gold 90 gsm	A		003R98839		90			OK All Trays	OK All Trays								
		003R98837			90			OK All Trays	OK All Trays								
			003R95838		90			OK All Trays	OK All Trays								
Xerox Colotech+ 90 gsm	A		003R94642		90			OK All Trays	OK All Trays								
		003R94641			90			OK All Trays	OK All Trays								
			003R97665		90			OK All Trays	OK All Trays								
Xerox Colour Impressions 90 gsm	A		003R97664		90			OK All Trays	OK All Trays								
		003R97663			90			OK All Trays	OK All Trays								
			003R98845		100			OK All Trays	OK All Trays								
Xerox Colotech+ Gold 100 gsm	A		003R98844		100			OK All Trays	OK All Trays								
		003R98842			100			OK All Trays	OK All Trays								
			003R95839		100			OK All Trays	OK All Trays								
Xerox Colotech+ 100 gsm	A		003R94647		100			OK All Trays	OK All Trays								
		003R94646			100			OK All Trays	OK All Trays								
			003R97103		100			OK All Trays	OK All Trays								
Xerox Colotech Natural White 100 gsm	A		003R97102		100			OK All Trays	OK All Trays								
			003R97668		100			OK All Trays	OK All Trays								
Xerox Colour Impressions 100 gsm	A		003R97667		100			OK All Trays	OK All Trays								
		003R97666			100			OK All Trays	OK All Trays								
			003R98849		120					OK All Trays	OK All Trays						
Xerox Colotech+ Gold 120 gsm	B		003R98848		120					OK All Trays	OK All Trays						
		003R98847			120					OK All Trays	OK All Trays						
			003R95840		120					OK All Trays	OK All Trays						
Xerox Colotech+ 120 gsm	B		003R94652		120					OK All Trays	OK All Trays						
		003R94651			120					OK All Trays	OK All Trays						
			003R97670		120					OK All Trays	OK All Trays						
Xerox Colour Impressions 120 gsm	A		003R97669		120					OK All Trays	OK All Trays						
		003R98685			120					OK All Trays	OK All Trays						
Uncoated Heavy Stocks	Decurler Setting Paper Type																
			003R98686		160							Trays 3 & 4	Trays 3 & 4				
Xerox Colour Impressions 160 gsm	A		003R98008		160							OK All Trays	OK All Trays				
		003R98007			160							OK All Trays	OK All Trays				
			003R98855		160							OK All Trays	OK All Trays				
Xerox Colotech+ Gold 160 gsm	A		003R98854		160							OK All Trays	OK All Trays				
		003R98852			160							OK All Trays	OK All Trays				
			003R95841		160							OK All Trays	OK All Trays				
Xerox Colotech+ 160 gsm	A		003R94657		160							OK All Trays	OK All Trays				
		003R94656			160							OK All Trays	OK All Trays				
			003R95957		160							OK All Trays	OK All Trays				
Xerox Colotech Natural White 160 gsm	A		003R95956		160							OK All Trays	OK All Trays				
			003R97969		200									OK All Trays	OK All Trays		
Xerox Colotech+ Gold 200 gsm	A		003R97968		200									OK All Trays	OK All Trays		
		003R97967			200									OK All Trays	OK All Trays		
			003R95842		200									OK All Trays	OK All Trays		
Xerox Colotech+ 200 gsm	A		003R94662		200									OK All Trays	OK All Trays		
		003R94661			200									OK All Trays	OK All Trays		
			003R95959		200									OK All Trays	OK All Trays		
Xerox Colotech Natural White 200 gsm	A		003R95958		200									OK All Trays	OK All Trays		
			003R97973		220									OK All Trays	OK All Trays		
		003R97971			220									OK All Trays	OK All Trays		
			003R95843		220									OK All Trays	OK All Trays		
Xerox Colotech+ 220 gsm	A		003R94669		220									OK All Trays	OK All Trays		
		003R94668			220									OK All Trays	OK All Trays		
			003R98977		250									OK All Trays*	OK All Trays		
Xerox Colotech+ Gold 250 gsm	A		003R98976		250									OK All Trays*	OK All Trays		
		003R98975			250									OK All Trays*	OK All Trays	Manual Duplex	
			003R95844		250									OK All Trays*	OK All Trays		
Xerox Colotech+ 250 gsm	A		003R94672		250									OK All Trays*	OK All Trays		
		003R94671			250									OK All Trays*	OK All Trays	Manual Duplex	
			003R97672		250									OK All Trays*	OK All Trays		
Xerox Colour Impressions 250 gsm (not recommended for rated speed mode)	A		003R97671		250									OK All Trays*	OK All Trays		
			003R97981		280									OK All Trays*	OK All Trays		
Xerox Colotech+ Gold 280 gsm	A		003R98980		280									OK All Trays*	OK All Trays		
		003R98979			280									OK All Trays*	OK All Trays	Manual Duplex	
			003R97099		280									OK All Trays*	OK All Trays		
Xerox Colotech+ 280 gsm	A		003R97098		280									OK All Trays*	OK All Trays		
		003R97097			280									OK All Trays*	OK All Trays	Manual Duplex	
			003R97985		300									OK All Trays*	OK All Trays		
Xerox Colotech+ Gold 300 gsm	A		003R97984		300									OK All Trays*	OK All Trays		
		003R97983			300									OK All Trays*	OK All Trays	Manual Duplex	
			003R97554		300									OK All Trays*	OK All Trays		
Xerox Colotech+ 300 gsm	A		003R97553		300									OK All Trays*	OK All Trays		
		003R97552			300									OK All Trays*	OK All Trays	Manual Duplex	

* Custom Paper Profiles (BTB) adjustment may be required to achieve optimum image quality. Contact your local Service Representative and refer to System Administration Guide for details

European Recommended Materials List - DocuColor 8000AP/8000/7000AP/7000

	Decurler Setting Paper Type	Standard Cut Sizes			Grammage Weight (g/m ²) Weight of the paper in grams per square metre	DC8000AP/8000/7000AP/7000 Trays/Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4	
		Weight Range Specification															
Instructions for printing one side (Simplex) or two sides (Duplex) ----->					60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm		
Coated Text or Book Stocks					Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
C25																	
Xerox Colotech+ Silk Coated 120 gsm	A		003R90356	003R90357	120					OK All Trays	OK All Trays						
		003R90355			120					OK All Trays	OK All Trays						
			003R90338		120					OK All Trays	OK All Trays						
Xerox Colotech+ Gloss Coated 120 gsm	A		003R90337		120					OK All Trays	OK All Trays						
		003R90336			120					OK All Trays	OK All Trays						
			003R90360		140							OK All Trays	OK All Trays				
Xerox Colotech+ Silk Coated 140 gsm	A		003R90359		140					OK All Trays	OK All Trays						
		003R90358			140					OK All Trays	OK All Trays						
			003R90341		140					OK All Trays	OK All Trays						
Xerox Colotech+ Gloss Coated 140 gsm	A		003R90340		140					OK All Trays	OK All Trays						
		003R90339			140					OK All Trays	OK All Trays						
Coated Heavy Stocks																	
C25																	
Xerox Colotech+ Silk Coated 170 gsm	A		003R90362	003R90363	170					OK All Trays	OK All Trays						
		003R90361			170					OK All Trays	OK All Trays						
			003R90344		170					OK All Trays	OK All Trays						
Xerox Colotech+ Gloss Coated 170 gsm	A		003R90343		170					OK All Trays	OK All Trays						
		003R90342			170					OK All Trays	OK All Trays						
Xerox Colotech+ Silk Coated 210 gsm	A		003R90365	003R90366	210							OK All Trays	OK All Trays				
(not recommended at rated speed)		003R90364			210							OK All Trays	OK All Trays				
			003R90347		210							OK All Trays	OK All Trays				
Xerox Colotech+ Gloss Coated 210 gsm	A		003R90346		210							OK All Trays	OK All Trays				
		003R90345			210							OK All Trays	OK All Trays				
Xerox Colotech+ Silk Coated 250 gsm	A		003R90368	003R90369	250							OK All Trays*	OK All Trays	OK All Trays			
		003R90367			250							OK All Trays*	OK All Trays	OK All Trays	Manual Duplex		
			003R90350		250							OK All Trays*	OK All Trays	OK All Trays			
Xerox Colotech+ Gloss Coated 250 gsm	A		003R90349		250							OK All Trays*	OK All Trays	OK All Trays			
(not recommended at rated speed)		003R90348			250							OK All Trays*	OK All Trays	OK All Trays	Manual Duplex		
Xerox Colotech+ Silk Coated 280 gsm	A		003R90371	003R90372	280									OK All Trays			
		003R90370			280									OK All Trays			
			003R90353		280									OK All Trays	Manual Duplex		
Xerox Colotech+ Gloss Coated 280 gsm	A		003R90352		280									OK All Trays*	OK All Trays		
(not recommended at rated speed)		003R90351			280									OK All Trays*	OK All Trays	Manual Duplex	
Super Gloss Coated Heavy Stocks																	
C15																	
Xerox Colotech+ Supergloss 135 gsm	A	Select 106-135 gsm mode. Load with coated side up.			135							OK All Trays	OK All Trays				
Image quality will not be as good on second side		003R97679															
Xerox Colotech+ Supergloss 160 gsm	A	Select 187-220 gsm mode. Load with coated side up.			160									OK All Trays	OK All Trays		
Image quality will not be as good on second side		003R97680			160									OK All Trays	OK All Trays		
Xerox Colotech+ Supergloss 210 gsm	A		003R97683	003R97684	210									OK All Trays	OK All Trays		
Image quality will not be as good on second side		003R97682			210									OK All Trays	OK All Trays		
(not recommended for rated speed)					210									OK All Trays	OK All Trays		
Xerox Colotech+ Supergloss 250 gsm	A	Select 221-300 gsm mode. Load with coated side up.			250										OK All Trays*	OK All Trays	
Image quality will not be as good on second side		003R97686		003R97687	250									OK All Trays*	OK All Trays		
(not recommended for rated speed)					250									OK All Trays*	OK All Trays	Manual Duplex	
Label Stock																	
Decurler Setting																	
Label Stock																	
Approximately																	
Xerox Colour Laser Printer Labels	C		003R93872		190									OK All Trays			
1 per A4		003R93873			190									OK All Trays			
6 per A4		003R93874			190									OK All Trays			
8 per A4		003R93875			190									OK All Trays			
14 per A4		003R97524			190									OK All Trays			
24 per A4		003R97288			190									OK All Trays			
Xerox Colotech+ Gloss Labels A4 1-up	C&A	003R97515			190 & 120									OK All Trays			
Xerox Colotech+ Matt 2-up CD Labels and CD Inserts Combi Box	C		003R98688		250									OK All Trays			
Xerox DuraPaper Label		003R98645			250									OK All Trays			
(polyolefin face material)		003R97344			250									OK All Trays			
Xerox Glossy White Self Adhesive Label for Conventional Toner	Default		003R97348		190									OK All Trays			
(not recommended for rated speed)		003R97245			190									OK All Trays			
Xerox Crystal Clear Self Adhesive Label for Conventional Toner	Default		003R97347		190									OK All Trays			
(not recommended for rated speed)		003R97244			190									OK All Trays			

* Custom Paper Profiles (BTB) adjustment may be required to achieve optimum image quality. Contact your local Service Representative and refer to System Administration Guide for details

European Recommended Materials List - DocuColor 8000AP/8000/7000AP/7000

		Standard Cut Sizes			Grammage Weight (g/m ²) Weight of the paper in grams per square metre	DC8000AP/8000/7000AP/7000 Trays/Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			
		Weight Range Specification				60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm	
Instructions for printing one side (Simplex) or two sides (Duplex)					Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
Specialties	Decurler Setting Paper Type				Various												
Xerox Colotech+ Supergloss 210 gsm A4 Prescored White 500 sheet box	A	Second side image quality will not be as good as side one. 003R97685			210									OK All Trays		OK All Trays	
Xerox DocuCard 500 sheet box	A	Maximum of 50 sheet stacks 003R97571			160									OK All Trays		OK All Trays	
Xerox ValuPeelCard Uncoated 500 sheet box	A	Maximum of 50 sheet stacks 003R97952			216									OK All Trays		OK All Trays	
Xerox ValuPeelCard Coated 500 sheet box	A	Maximum of 50 sheet stacks 003R97953			216									OK All Trays		OK All Trays	
Xerox ValuPerfCard Uncoated 500 sheet box	A	Maximum of 50 sheet stacks 003R97690			216									OK All Trays		OK All Trays	
Xerox DocuMagnet Coated 500 sheet box	A	Max. 50 sheet stack. Load short edge feeding, magnet trailing. 003R96071			Magnet 430 micron											OK All Trays Manual Duplex	
Xerox DocuMagnet Uncoated 500 sheet box	A	Max. 50 sheet stack. Load short edge feeding, magnet trailing. 003R96072			Magnet 430 micron											OK All Trays Manual Duplex	
Xerox Premium NeverTear*	Default	Select Coated 136-186 gsm Transfer=130. Each batch run should not be more than 500 duplex. Must run 50 sheets paper between batches. Static in sheets may cause issues. 003R98056			95 microns									OK All Trays		OK All Trays	
		Select Coated 136-186 gsm Transfer=150. Each batch run should not be more than 500 duplex. Must run 50 sheets paper between batches. Static in sheets may cause issues. 003R98058			120 microns									OK All Trays		OK All Trays	
Xerox DuraPaper	A	Select Uncoated 187-220 gsm mode. Load image side up. 003R97513			250 microns									OK All Trays		Manual Duplex	
Xerox Colotech Supergloss Document Folder (not recommended for rated speed)	A	Select Coated 221-300 gsm mode for glossy side, Uncoated 221-280 gsm for matt side. 003R97634			250											OK All Trays Manual Duplex	
Xerox Laser Business Cards 10-up	A	Select Uncoated 187-220 gsm mode in Tray 3 - image side up. 003R97512			195											OK All Trays Manual Duplex	
Xerox Laser Window GraphiX Clear window decal	A	Select Coated 187-220 gsm mode - image side up. 003R97494			125 micron									OK All Trays		OK All Trays	
Xerox Laser Window GraphiX Opaque White window decal	A	Select Coated 187-220 gsm mode - image side up. 003R97511 003R97539			125 micron									OK All Trays		OK All Trays	
Transfer Paper	Decurler Setting Paper Type																
Xerox Universal Transfer Paper	D	Select Coated 136-186 gsm mode - image side up. Each batch run should not exceed 500 sheets. 100 sheets Colotech+ Paper should be run between batches. No more than 500 sheets per day. 003R93544												OK All Trays OK All Trays			
Tab Stock See Specialty Media Guide or Xerox.com/support for instructions	Decurler Setting Paper Type																
Xerox Colotech Tabs White 100x5 Reverse Collated	B	Feed long edge first, tabs trailing. 003R97231			200									OK All Trays		OK All Trays	
Xerox Colotech Tabs White 50x10 Reverse Collated	B	003R97232			200									OK All Trays		OK All Trays	
Xerox Reinforced Tabs White 100x5 Reverse Collated	B	003R97229			200									OK All Trays		OK All Trays	
Transparencies	Decurler Setting Paper Type																
Xerox Universal Transparency with Paper Backing (not recommended for rated speed)	Default	For high print quality Select Uncoated 221-300 gsm mode. Load transparency facing up. 003R98199			100 micron 100 micron											OK All Trays OK All Trays	
Xerox Universal Transparency with Paper Backing (not recommended for rated speed)	Default	For high speed (standard print quality) Select Uncoated 187-220 gsm mode. Load transparency facing up. 003R98199			100 micron 100 micron									OK All Trays OK All Trays			
Xerox Colobind Gloss Covers	Decurler Setting Paper Type																
Xerox Colobind Gloss Covers Spine width 1.5 mm Spine width 3 mm Spine width 6 mm Spine width 9 mm Spine width 12 mm		Limit tray capacity to 50 sheets. Image quality can vary from good to fair depending on score quality. Slightly degraded image quality on uncoated side. Image coated side 1st to minimize glass/roll streaking. Do not image within 6mm around the score lines. Manual duplex printing only. Postscript custom size required for 6mm, 9mm and 12 mm spines. 003R98022			210											OK All Trays Manual Duplex	
		003R98023			210											OK All Trays Manual Duplex	
		003R98024			210											OK All Trays Manual Duplex	
		003R98025			210											OK All Trays Manual Duplex	
		003R98026			210											OK All Trays Manual Duplex	

* Custom Paper Profiles (BTB) adjustment may be required to achieve optimum image quality. Contact your local Service Representative and refer to System Administration Guide for details

European Recommended Materials List - DocuColor 8000AP/8000/7000AP/7000

		Standard Cut Sizes			Grammage Weight (g/m ²) Weight of the paper in grams per square metre	DC8000AP/8000/7000AP/7000 Trays/Weight Selection and Best Practices for Operation										
		A4 210x297 mm	A3 297x420 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4
Weight Range Specification ----->					60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm	
Instructions for printing one side (Simplex) or two sides (Duplex) ----->					Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex
Carbonless Paper	Decurler Setting Paper Type				Approximately											
Xerox Premium Digital Carbonless	A	IOT Common Software V2.191 must be installed and fan disabled prior to use. Contact Local Service Representative and refer to System Administrator Guide for details.														
CB Singles White		003R99069			82			OK All Trays								
CB Singles White (Perforated along long edge)		003R99088			82			OK All Trays								
CB Singles Yellow		003R99080			82			OK All Trays								
CB Singles Pink		003R99083			82			OK All Trays								
CB Singles Blue		003R99082			82			OK All Trays								
CB Singles Green		003R99081			82			OK All Trays								
CFB Singles White		003R99070			86			OK All Trays								
CFB Singles Yellow		003R99071			86			OK All Trays								
CFB Singles Yellow (Perforated along long edge)		003R99091			86			OK All Trays								
CFB Singles Pink		003R99074			86			OK All Trays								
CFB Singles Pink (Perforated along long edge)		003R99093			86			OK All Trays								
CFB Singles Blue		003R99072			86			OK All Trays								
CFB Singles Green		003R99073			86			OK All Trays								
CF Singles White		003R99075			82			OK All Trays								
CF Singles Yellow		003R99076			82			OK All Trays								
CF Singles Pink		003R99077			82			OK All Trays								
CF Singles Blue		003R99078			82			OK All Trays								
CF Singles Green		003R99079			82			OK All Trays								
A4+ CF Singles Yellow		003R99639			82			OK All Trays								
A4+ CF Singles Pink		003R99638			82			OK All Trays								
CF Singles Tag Cream		003R99146			170									OK All Trays		
CF Singles Tag White		003R99147			170									OK All Trays		
A4+ CF Singles Tag Cream		003R99640			170									OK All Trays		
A4+ CF Singles Tag Pink		003R99641			170									OK All Trays		
2-Part White/Yellow		003R99105	003R99133		82/82			OK All Trays								
2-Part White (Perforated along long edge)/Yellow		003R99084			82/82			OK All Trays								
2-Part White/Pink		003R99107	003R99134		82/82			OK All Trays								
3-Part Straight White/Yellow/Pink		003R99108	003R99135		82/86/82			OK All Trays								
3-Part Straight White (Perforated LE)/Yellow (Perforated LE)/Pink		003R99086			82/86/83			OK All Trays								
3-Part Reverse Pink/Yellow/White	003R99109			82/86/85			OK All Trays									
4-Part Straight White/Yellow/Pink/Blue	003R99111			82/86/86/82			OK All Trays									
4-Part Reverse Blue/Pink/Yellow/White	003R99112			82/86/86/82			OK All Trays									

* Custom Paper Profiles (BTB) adjustment may be required to achieve optimum image quality. Contact your local Service Representative and refer to System Administration Guide for details